Leonardo 300

PHOTOPOLYMER FILM LAMINATION & COVER SHEET REMOVAL SYSTEMS





Milan - ITALY www.microcontrol.org

Leonardo 300

PHOTOPOLYMER FILM LAMINATION SYSTEM

Process Station



Microcontrol Electronic history

Established in 1976, Microcontrol Electronic introduced the **first worldwide**automatic Taper and Detaper on the market in 1984.

Since then hundreds of equipment has been sold all over the world to the most important companies such as Atmel, IBM, Infineon, Intel, Micron, Motorola, Philips, STM and TI.

From this experience and improved technology we created **Leonardo 300.**This system allows to laminate photopolymer film, used in BUMPING, WAFER LEVEL PACKAGING process and MEMS application to create multilevel structures containing heavy topography or pre etched features on silicon wafers or any other substrate including glass and thru holes wafers from 200 to 300 mm.

LOWEST TAPE CONSUMPTION

"GAP CONTROL AND ROLL WIDTH OPTIMIZATION"

CHUCK ROLLER TEMPERATURE

Leonardo 300
COVER SHEET
REMOVAL SYSTEM







Leonardo 300 ution!

Leonardo 300 Lamination

SYSTEM SPECIFICATIONS

WAFER SIZE
THROUGHPUT
CENTERING / Alignment
TAPE COMPATIBILITY
MINIMUM TAPE WIDTH
N° of WAFERS WITH 100 m ROLL
FOOT PRINT
CE marking
SEMI Standard
SECS-GEM SEMI compliance
WAFER ID / CASSETTE ID
LOADPORT SYSTEM
M.T.B.F.

8" - 12"
PROCESS DEPENDING (average of 50 wfrs/h)
CONTACLESS VISION SYSTEM
ALL KIND OF TAPES
8" - 215 mm 12" - 315 mm
8" 470 Wfrs - 12" 320 wfrs
1,9 m²
Full compliance
Full compliance
Option
Option OCR - DOT matrix - BCR
Option
550 hrs

Leonardo 300 Cover Sheet Removal

1 hr

SYSTEM SPECIFICATIONS

WAFER SIZE
THROUGHPUT
CENTERING / Alignment
TAPE COMPATIBILITY
FOOT PRINT
CE marking
SEMI Standard
SECS-GEM full compliance
WAFER ID / CASSETTE ID
LOADPORT SYSTEM
M.T.B.F.
M.T.T.R.

8" - 12"
65 wfrs/h
CONTACLESS VISION SYSTEM
ALL KIND OF TAPES
1,9 m²
Full compliance
Full compliance
Option
Option
Option OCR - DOT matrix - BCR
Option
550 hrs
1 hr



via Giuba, 11 - 20132 Milan - ITALY phone +39 02 28.31.44.20 fax +39 02 28.71.777

e-mail: info@microcontrol.org www.microcontrol.org







